

# Smart™ 151S

## Introduction

Smart™ 151S, metallocene LLDPE, is an **ethylene-octene copolymer** produced via Nexlene™ technology. Smart™ 151S performs well in a wide range of various food & non-food packaging films with excellent sealing property, impact strength, and processability.

Typical Performance:

- Excellent low seal initiation temperature and hot tack strength
- Superior impact strength and transparency
- Outstanding bubble stability & processability

Compiles with:

- US. FDA 21 CFR 177.1520
- EU. No 10/2011

Additives:

- Antiblock: 2000 ppm
- Slip: 1000 ppm

## Properties

		Typical Values	Unit	Test Method	
<b>Resin Properties</b>	Density	0.916	g/cm <sup>3</sup>	ASTM D792	
	Melt index (2.16 kg @190°C)	1.0	g/10min	ASTM D1238	
	Melting temperature	113	°C	SK Method	
	Vicat softening temperature	103	°C	ASTM D1525	
<b>Film Properties</b>	Film thickness - tested	40	µm	ASTM D374	
	Dart impact strength	900	g	ASTM D1709A	
	Haze	11	%	ASTM D1003	
	Seal initiation temperature	104	°C	SK Method <sup>1</sup>	
	Elmendorf tear strength	MD	12	g/µm	ASTM D1922
		TD	22	g/µm	ASTM D1922
	Tensile strength at break	MD	520	kg/cm <sup>2</sup>	ASTM D882
		TD	550	kg/cm <sup>2</sup>	ASTM D882

*Technical Information*

Elongation at break	MD	580	%	ASTM D882
	TD	650	%	ASTM D882
Secant modulus (1%)	MD	1460	kg/cm <sup>2</sup>	ASTM D882
	TD	1720	kg/cm <sup>2</sup>	ASTM D882

<b>Extrusion Condition</b>	<ul style="list-style-type: none"> <li>• Screw size: 35 mm</li> <li>• Die diameter: 100 mm</li> <li>• Die gap: 1 mm</li> <li>• Blow-up ratio: 2.1</li> <li>• Melt temperature: 160-180 °C</li> </ul>
----------------------------	--

<sup>1</sup> Temperature at which 0.4 kg/25.4 mm heat seal strength is achieved

**Notes**

These are **typical values** and are **not be construed as specifications**. The physical properties are highly dependent on the manufacturing conditions. So customers should confirm performances by their own tests.

*For additional sales, order and technical assistance*

**Head office** SK Global Chemical Co.,LTD  
26 Jong-ro, Jongno-gu,  
Seoul, Korea  
TEL +82-2-2121-5052

**TS&D** SK innovation Global Technology  
325 Exporo, Yueseong-gu,  
Daejeon, Korea  
TEL +82-42-609-8623